

HALO H₂O in N₂O Trace Level Moisture Analyzer for Nitrous Oxide

GASES & CHEMICALS	CEMS	ENERGY	SEMI & HB LED	ATMOSPHERIC	LAB & LIFE SCIENCE
-------------------	------	--------	---------------	-------------	--------------------

Designed for trace level moisture analysis in nitrous oxide, the HALO H₂O offers:

- Low parts per billion (ppb) moisture detection capability in medical N₂O
- Absolute measurement (freedom from calibration gases)
- Wide dynamic range—over four orders of magnitude
- Low cost of ownership and operational simplicity
- Clean technology-no external calibration gases required
- Compact analyzer footprint

The HALO H_2O analyzer provides users with the unmatched accuracy, reliability, speed of response and ease of operation that users of Tiger Optics analyzers have come to expect. Featuring Tiger Optics' powerful Cavity Ring-Down Spectroscopybased moisture sensor in a compact and economical package, this versatile analyzer allows users to measure trace moisture in nitrous oxide (N₂O) and other gases. Users can also expect significant cost savings, with no need for periodic sensor maintenance, span calibrations, purifier replacements, and pump rebuilds. As a result, the HALO H₂O analyzer is ideally suited to many applications where moisture measurement is extremely critical. These applications include process control, continuous quality control, and cylinder analysis for medical and calibration gases and more.



HALO H₂O in N₂O Trace Level Moisture Analyzer for Nitrous Oxide



Performance

Operating range	See table below		
Detection limit (LDL, $3\sigma/24h$)	See table below		
Precision (1 σ , greater of)	± 0.75% or 1/3 of LDL		
Accuracy (greater of)	± 4% or LDL		
Speed of response	< 1 minute to 90%		
Environmental conditions	10°C to 40°C		
	30% to 80% RH (non-condensing)		
Storage temperature	–10°C to 50°C		

Gas Handling System and Conditions

Wetted materials	316L stainless steel		
	10 Ra surface finish		
Gas connections	1/4" male VCR inlet and outlet		
Leak tested to	1 x 10 ⁻⁹ mbar l / sec		
Inlet pressure	10 – 125 psig (1.7 – 9.6 bara)		
Flow rate	Up to 1.8 slpm		
Sample gases	Most inert, toxic, passive		
	and corrosive matrices		
Gas temperature	Up to 60°C		

Dimensions	H x W x D [in (mm)]
Standard sensor	8.73 x 8.57 x 23.6 (222 x 218 x 599)
Sensor rack	8.73 x 19.0 x 23.6 (222 x 483 x 599)
(fits up to two sensors)	
Weight	
Standard sensor	28 lbs (12.7 kg)
Electrical and Interfaces	
Platform	Max series analyzer
Alarm indicators	2 user programmable
	1 system fault
	Form C relays
Power requirements	90 – 240 VAC, 50/60 Hz
Power consumption	40 Watts max.
Signal output	Isolated 4–20 mA per sensor
User interfaces	5.7" LCD touchscreen
	10/100 Base-T Ethernet
	USB, RS-232, RS-485
	Modbus TCP (optional)
Data storage	Internal or external flash drive
Certification	CE Mark

Performance, H ₂ O:	Range	LDL (3σ)	Precision (1ơ) @ zero
In Nitrogen	0 – 15 ppm	2.2 ppb	0.8 ppb
In Nitrous Oxide (N ₂ O)	0 – 20 ppm	7.5 ppb	2.5 ppb
In Argon	0 – 6 ppm	1.0 ppb	0.35 ppb
In Helium	0 – 3 ppm	0.5 ppb	0.2 ppb
In Hydrogen	0 – 12 ppm	1.9 ppb	0.7 ppb
In Oxygen	0 – 8 ppm	1.2 ppb	0.4 ppb

Contact us for additional analytes and matrices. U.S. Patent # 7,277,177

Tiger Optics, LLC

275 Gibraltar Road, Horsham, PA 19044 Phone: +1 (215) 656 4000 · Fax: +1 (215) 343 7168 sales@tigeroptics.com · www.tigeroptics.com



